Tempy.air Series

Non-contact Medical Device for Automatic Body Temperature Measurement

Applied an intuitive display that anyone can use easily.





- 2. Quick & accurate temperature measurement even at long distances within 50cm (20in)
 - **3.** Access control function

Facial recognition that identifies if a mask is being worn
Automatic warning in case of abnormal body temperature **4.** Built-in temperature sensor (7 million units sold in the 1H of last year), the pinnacle of exceptional technology produced by Tempus



Specifications

Temperature sensor	Pixel The margin of measurement error Measurement distance Measurement range / view angle	4 X 4 pixels ± 0.3°C (±0.5°F) Optimal distance 30cm (12in) 34.0°C ~ 42.0 °C (93.2°F ~ 107.6°F) / 18° x 18°
Camera	Resolution Lens Image Sensor	2M, 1920(W) X 1080(H) F2.0 1/2.7"
Screen	Size Resolution	4" 800 X 480(Pixels)
Process	MCU OS memory	V526 Linux TEMPYAIR 4.9.118 armv7l GNU / Linux 256 Mbyte
General Specifications	Power The power supply method could be changed according to user environment(Equipped with a supplementary battery more than 10,000mAh). Electric energy consumption Size Weight Operating temperature range	INPUT : 100-240V 50~60HZ 0.4A OUTPUT : 5V /1A Adopter for medical devices (UL) 5V / MAX 500mA 112.5(W) X 102.5(H) X 33.6(D) 160g (5.6oz) 22°C ~ 28°C (71.6°F ~ 82.4°F)
Interface	Power Button LED Speaker USB Host	USB C type Power On / Off Body temperature measurment : Green LED Warning alarm : Red LED MAX 1W USB 2.0 A Type
Function	Temperature display Unit of measurement Measuring time Facial recognition Mask recognition UI interface Firmware upgrade Language Abnormal temperatue alarm	°C or °F 0.1 °C / 0.1 °F About 1second Supported Supported Supported (USB Host) English/French/Spanish/Korean/Japanese/Chinese German/Vietnamese/Persian Supported (Screen, Sound, LED display)

Certification



Tempy.air Series Cradle

Tempy.air Series Cradle has been produced to be furnished in various places in combination with Tempy.air Series(contact-free face recognition thermometer). Depending on the place to be used, a different kind of cradle can be selected.



The specifications above could be changed without notice. The weight marked on the model does not include the non-contact face recognition thermometer.

Manufacturer / Tempus (01811) 12F Seoul Techno Park, 232 Gongneung-ro Nowon-gu, Seoul T 82. 2. 944. 6513 F 82. 2. 944. 6522 www.tempuselec.com